

SWIT®

CL-15 LED CAMERA LIGHT

Ver: A

USER MANUAL

SWIT Electronics Co.,Ltd.

Tel:+86-25-85805753
Fax:+86-25-85805296
http://www.swit.cc
E-mail: contact@swit.cc

Thank you for choosing SWIT products. Please read the instructions before using, and keep it for future reference.

Specification

| | |
|-------------------|--------------|
| Model | CL-15 |
| LED | 416 PCS |
| Luminance | 550 Lux@1m |
| CRI | 95 |
| TLCI | 97 |
| Half beam angle | 65° |
| Color temperature | 3200K~6500K |
| Power | About 15W |
| Input voltage | DC 7.2V-8.4V |
| Dimension | See fig.1 |
| Net weight | About 145g |

Cautions

1. Do not disassemble light or touch the interior with metal objects to avoid damage;
2. Do not stain and damage to the front panel of the lamp to avoid affecting the use effect
3. Do not store the light in dusty or wet environment to avoid damage.
4. Only use the light in the temperature range of -10°C~40°C.

Maintenance

1. Use soft dry cloth to clean the light and front panel. Can also Use a soft cloth dipped slightly in a neutral detergent solution for cleaning, but wipe with a soft dry cloth after cleaning.
2. Do not use wet cloth, absolute alcohol, benzene to wipe the light panel or soft panel, otherwise will damage the soft panel.

Appearance




Fig.1 CL-15 Overall Dimension




Fig. 2 CL-15 Front view




Fig.3 CL-15 Back view




Fig.4 CL-15 Upward view

- ① LED Panel
- ② DV Battery mount slot
- ③ Battery unlock button
- ④ Power indicator
- ⑤ Color temperature knob
- ⑥ Power switch
- ⑦ Intensity knob
- ⑧ 1/4" mounting hole

Operation instructions

1. Power supply

This product only support SONY NP-F model battery, please choose the battery according to below list:

| | |
|--------------------|-----------------------|
| Supporting battery | Recommend battery |
| SONY NP-F970/770 | S-8975/8972/8970/8770 |

2. Installation

The bottom of the light is provide with 1/4" mounting hole(Fig.4 ⑧), can mount on tripod directly or install on the camera with pan-tilt.

3. Intensity control

Control by【Intensity knob】(Fig.3 ⑦), adjustment range:0%~100%.

4. Color temperature control

Control by【Color temperature knob】(Fig.3 ⑤), adjustment range: 3200K~6500K.

Packing list

| No. | Details | Quantity |
|-----|---------------|----------|
| 1 | CL-15 | x 1 |
| 2 | Soft panel | x 1 |
| 3 | User manual | x 1 |
| 4 | Warranty card | x 1 |